Test Date - 23/10/2018

MICRON

MAN - ALPACA FIBRE ANALYSIS

Ravenswood Alpacas 2272 Queens Pinch Rd Mudgee NSW 2850

Date Sample Taken - 13/10/2018

Contact :- Micron Man Our Phone (08)94181733 P.O. Box 1423 Bibra Lake W.A. 6965

Group ID. Full Group

Test No. RAV81019

Wool Growth - 12 months

Age at Sample Date -

23.3 um

5.5 um

Micron Profile Graph

months

90 Micron

214175 Eartag:

Micron Deviation : -2.2 um

10.9 >30 :

23.6 % CV 5.2 % CE 23.2 um SF CF 89.1 %

Micron :


60

SD

CRV 40.0 Deg/mm

28.8 Deg/mm Total Fibres counted: SDC : 6558

OFDA2000 Alpaca Calibration: Trim High ON



10 EXPLANATION OF TERMS

0

- FD: Overall average Fibre Diameter measured in micron (um).
- Standard Deviation, measures the distance either side of the average fibre diameter where approx 2/3 of the fibre diameters lie.
- Coefficient of Variation = SD as a percentage of the average micron
- Coarse Edge. The percentage of fibres that lie over 10 microns greater than the average fibre diameter.
- Comfort Factor. The percentage of fibres less than 30 microns
- Spinning Fineness. Combine Micron & CV to a single number to represent the spinning quality expressed in microns.
- >30 : The percentage of fibres greater than 30 microns
- Fibre Curvature is the average curvature or bending over one millimetre length. It is related to crimp frequency and is measured in degrees per millimetre (Dg/mm)
- Standard Deviation of Curvature is the variation of curvature for the above measurement. SDC is related to crimp definition and measured in degrees per millimetre (Dg/mm).
- TRIM :
- SDC is related to Climp definition.

 If sample is tested with Trim High ON, then the result is trimmed to 4 SD's above average FD.

 If sample average FD=22um and SD=5um then Trim High ON = 22+20=44um. Measurement above 44um is removed.

 Trim High OFF means no coarse tail trimming on the sample tested that gives a closer result to other instruments.
- GCF: Grease Correction Factor is the FD adjustment needed when measuring greasy Alpaca fibre @ 20um-0.6um = 19.4um